

*Technical Data Sheet***Serie PWF****PASTE POLIV. A PIGMENTO FLUORESCENTE
ALL'ACQUA****PRODUCT DESCRIPTION:**

Fluorescent pigment concentrate to be mixed with **Colortech** system converters.

APPLICATIONS:

They are used by mixing them with **KW** converters (Resins) from the **Colortech** tinting system to produce finished enamels in various fluorescent colours.

They are particularly suitable for 2K converters such as our **KW711, KW721, KW723, KW773** and 1K converters such as our KW374. They can also be used with 1K resins such as KW431, KW433, KW631 and KW634.

Application on a white undercoat-primer is recommended in order to maximise colour rendering and the intensity of the fluorescent effect.

The use of PWF pastes for outdoor applications is not recommended.

PRODUCT PREPARATION:

PWF series pastes are added to pre-weighed **KW** series resins according to the chosen colour formulations and placed in the **Colortech**.

After adding the pastes to the converter, they must be dispersed immediately, preferably using a mechanical shaft agitator (not a gyroscope) or, alternatively, for small quantities of finished product (1–2 litres), by vigorous manual stirring.

SAFETY PRECAUTIONS:

Strictly adhere to the instructions on the label and in the safety data sheet.

STORAGE CONDITIONS:

The storage area must be dry and maintained at a temperature between +10°C and +35°C.

Water-based products should beware of frost.

The data and information contained in this sheet are based on our experience and on thorough laboratory tests. However, as the varnishing process involves a series of operations beyond our control, they do not in any way constitute a guarantee of the final performance of the process itself.

Rev. No. 00 of 01/12/2025